
Type sheet Vacuum relief valve KITO® VS/oP-...



Application

As end-of-line armature on storage tanks and silos in which powder products and granulates are stored. Ventilation is provided to prevent dangerous vacuum. All moving parts are outside the storage room.

Dimensions (mm) and settings (mbar)







DN			н	ka	cotting
DIN	ASME	D	П	kg	setting
25 PN 40	1"	205	130	3	
50 PN 16	2"	170	133	5	
80 PN 16	3"	285	170	8	
100 PN 16	4"	330	180	10	2 - 50
125 PN 16	5"	295	240		2 - 50
150 PN 16	6"	350	248	26	
200 PN 10	8"	550	308	36	
250 PN 10	10"	550	350		

Indicated weight refers to the standard design

Example for order

KITO® VS/oP-50

(design with flange connection DN 50 PN 16)

Without EC certificate and C€-marking

page 1 of 2

 KITO Armaturen GmbH
 J
 +49 (0) 531 23000-0

 Grotrian-Steinweg-Str. 1c
 ∃
 +49 (0) 531 23000-10

 D-38112 Braunschweig
 □
 www.kito.de

 VAT Reg.No DE812887561
 □
 info@kito.de

D 12.4 N o7-2022

Date: 07-2022
Created: Abt. Doku KITO
Design subject to change

Type sheet Vacuum relief valve KITO® VS/oP-...



Design


	standard	optionally		
housing	steel	stainless steel mat. no.1.4571		
inner face of housing	PTFE-coated			
gasket	HD 3822	PTFE		
valve seat, valve spindle	stainless steel mat. no. 1.4571			
valve sealing	NBR	Viton, PTFE		
compression spring	stainless steel mat. no. 1.4310			
weather hood	stainless steel mat			
flange connection	drilled to EN 1092-1 type A	drilled to ASME B16.5 Class 150 RF		
_	(partial with threaded holes for stud bolts)			

Performance curves

Flow capacity V based on air of a density $p = 1.29 \text{ kg/m}^3$ at T = 273 K and atmospheric pressure p = 1.013 mbar. For other gases the flow can be approximately calculated by

$$\overset{\cdot}{V}_{40\%} = \overset{\cdot}{V}_b \cdot \sqrt{\frac{\rho_b}{1.29}} \qquad or \qquad \overset{\cdot}{V}_b = \overset{\cdot}{V}_{40\%} \cdot \sqrt{\frac{1.29}{\rho_b}}$$

The indicated flow rates will be reached by an accumulation of 40% above valve's setting (see DIN 4119). If the allowable overpressure is less 40%, please consult der factory for the corrected volume flow.



info@kito.de

)

 \bowtie

D 12.4 N 07-2022 Date: Abt. Doku KITO Created: Design subject to change